






- Note:
- Material
 - 1.1: Housing: LCP UL94-V0 Color:Natural.Or Black
 - 1.2: Actuator: LCP UL94-V0 Color:Black Or Natural
 - 1.3: Contact: Phosphor Bronze.
 - 1.4: LEG: Phosphor Bronze.
 - Plating
 - 2.1: Contact: See Part Number.
 - 2.2: LEG: Matte Tin Plating Over Nickel.
 - Rating:
 - 3.1: Operating Voltage: 30V AC/DC.
 - 3.2: Current Rating: 0.2A AC/DC.
 - 3.3: Operating Temperature:-55°C~+85°C.



Applicable FPC



FPC/FFC Insert Direction
Recommended P.C.B Layout



Number of Contacts	Dimension				
	A	B	C	D	E
11	4.80	2.40	3.00	3.70	4.30
13	5.40	3.00	3.60	4.30	4.90
15	6.00	3.60	4.20	4.90	5.50
17	6.60	4.20	4.80	5.50	6.10
19	7.20	4.80	5.40	6.10	6.70
21	7.80	5.40	6.00	6.70	7.30
23	8.40	6.00	6.60	7.30	7.90
25	9.00	6.60	7.20	7.90	8.50
27	9.60	7.20	7.80	8.50	9.10
29	10.20	7.80	8.40	9.10	9.70
31	10.80	8.40	9.00	9.70	10.30
33	11.40	9.00	9.60	10.30	10.90
35	12.00	9.60	10.20	10.90	11.50
37	12.60	10.20	10.80	11.50	12.10
39	13.20	10.80	11.40	12.10	12.70
41	13.80	11.40	12.00	12.70	13.30
45	15.00	12.60	13.20	13.90	14.50
49	16.20	13.80	14.40	15.10	15.70
51	16.80	14.40	15.00	15.70	16.30
57	18.60	16.20	16.80	17.50	18.10
61	19.80	17.40	18.00	18.70	19.30
67	21.60	19.20	19.80	20.50	21.10
71	22.80	20.40	21.00	21.70	22.30
73	23.40	21.00	21.60	22.30	22.90

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差參考表

X.X	±0.30	X.X°	±5°
X.XX	±0.20	X.XX°	±2°
X.XXX	±0.10	X.XXX°	±1°

东莞市高钺达电子科技有限公司



TITLE:
產品名稱: FPC 0.3Pitch 1.0H ZIF
R/A Connector

DWG NO:
產品料號: FPCXX-T1S1-2023-AC

DATE	SCALE	UNIT	PAGE
20111004	1:1	mm	1/1

本产品需符合 ☐ RoHS ☐ SONY00259 ☒ HF ☐ 其他
※禁止使用本公司所禁用有毒物质

REV	DESCRIPTION	ECN.NO	DATE
C	添加11PIN规格	20140331001	03/31'14
B	0.70改为0.80	20130520001	05/20'13
A	-----		02/18'13