






REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		1.5ZHW A 初	2018-04-22			



PCB Layout



温度范围: -25℃~85℃
额定电压: 100V AC/DC
额定电流: 1A AC/DC
接触电阻: ≤0.02Ω
绝缘电阻: ≥500MΩ
耐 压 值: 500V AC/minute
适用基板厚度: 1.6mm

技术要求:

- 1) 材质: 见附表;
- 2) 电镀: 见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。

GENERAL TOLERANCES			
DIM	TOL	DIM	DEG
X.		X°.	±3.00°
X.X	±0.35	X.X°	±2.00°
X.XX	±0.25	X.XX°	±1.00°
X.XXX	±0.15	X.XXX°	

2	PIN	n PCS	材质: 黄铜, 电镀: 镀亮锡			
1	Housing	1 PCS	材质: PA66 (UL94V-0), 颜色: 本色			
NO.	NAME	QTY	DESCRIPTION			
东莞市文章济美电子有限公司						
DRAW :	瞿寿坤	2018-04-22	TITLE: WAFER 1.5ZHWA 卧式 DIP		DRAW NAME: 5001-ZH0015D-**P1-00-B	
DESIGN:	瞿寿坤	2018-04-22				
CHECK:	胡海萍	2018-04-22	SERIES: 1502 SERIES			
APPROVED	胡海萍	2018-04-22	P/N:		DRAW NO.	
CUSTOMER DRAWING			REV. 1.00	SCALE N/A	UNIT: mm	SHEET: 1/1
						