







RECOMMENDED P.C.B LAYOUT

INSPECTION DIMENSION:(A)~(M)



NOTES

1. MATERIAL:
Housing:PBT, UL 94V-0
Terminal:Copper Alloy.
Shell:SPCC.
Boardlock:Copper Alloy.
Bracket:Zinc Alloy.
Screw:Copper Alloy.
2. FINISH:
Terminal:Gold Plated over Nickel at Contact Area.
Tin Plated over Nickel at Solder Area.
Shell:Nickel Plated.
Boardlock:Tin Plated.
Bracket:Nickel Plated.
Screw:Nickel Plated.
3. This Product is LEAD-FREE & RoHS Compliance Product.

SPECIFICATIONS

1. D-SUB
- 1.1 Voltage: 250 VAC(RMS) Max.
- 1.2 Current Rating: 3 Ampere per Contact
- 1.3 Contact Resistance: 25 Milliohms Max.
- 1.4 Insulation Resistance: 5000 Megohms Min.
- 1.5 Dielectric Withstanding Voltage: 1000V AC(RMS)
- 1.6 Total Mating Force: 6.0 Kgf Max.
- 1.7 Total Unmating Force: 1.2 Kgf Min.
- 1.8 Operating Temperature: -55°C to +85°C



深圳市华宇创精密电子有限公司

TOLERANCE:		DRAWN BY :	DATE :	PART NAME:	
X.X ±0.30		陈一鸣	2014-02-23	HDR15母对HDR15母 钎锁5.08 间距15.88	
X.XX ±0.25					
X.XXX ±0.15					
X: ±2° X.X° ±0.5°		CHECKED BY:	DATE :	PART NO.	HYCW56-VGA30B-158B
		马跃	2014-02-23	MOLD NO.	
				APPROVED BY:	DATE :
SCALE:1:1	SIZE: A4	邱国夷	2014-02-23	SHEET NO.	1 OF 1