



A



SECTION A-A
SCALE 1:1

Specifications

A. Material

Insulator: LCP, UL94 V-0, Black
Contact: Copper Alloy, T=0.12mm
Mid Plate: Stainless Steel, T=0.15mm
Shell: Stainless Steel, T=0.30mm

B. Plating

Contact Area: 3u" Au over 60u' min. Nickel
Solder Tails: 1u" Au over 60u" min. Nickel
Shell: 50u" min. Nickel
Mid Plate: No Plating

C. Electrical

Current Rating: 5.00A collectively for VBus & GND pins
1.25A for A5/B5 pins
0.25A for all other pins

Voltage Rating: 48V

Power Rating: 240W

Contact Resistance: 40mΩ max initial
50mΩ max after test

Dielectric Withstanding Voltage: 100V AC
Insulation Resistance: 100MΩ min.

D. Mechanical & Environmental




Operating Temperature: -25t to +85t

Mating Force: 5 to 20 N.

Unmated Force: 6 to 20 N after test


Durability: 10,000 cycles

B



C

D




E

Part Number			Product Description		
PTCFW-H22A-032			USB 2.0 Type C Receptacle, Horizontal, SMT, Mid Mount, 1.0mm Offset, 16 Pin		
DWG.No.	P-TCF-044		Tolerances Unspecified		Units: Metric(mm)
Revision	A0		X.X ±0.35	X° ±5°	 ROHS COMPLIANT 2011/65/EU Deca-BDEV
Designed	Lee	10/10/20	X.XX ±0.25	X.X° ±2°	
Approved	Allen	10/10/20	X.XXX ±0.15		





www.szywf.com.cn
www.szywf.cn


Sheet No. 1/3






PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SUB2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND



Part Number			Product Description			 WF <i>Connecting the Future</i> www.szywf.com.cn www.szywf.cn
PTCFW-H22A-032			USB 2.0 Type C Receptacle, Horizontal, SMT, Mid Mount, 1.0mm Offset, 16 Pin			
DWG.No.	P-TCF-044		Tolerances Unspecified		Units: Metric(mm)	
Revision	A0		X.X ±0.35	X° ±5°		
Designed	Lee	10/10/20	X.XX ±0.25	X.X° ±2°		
Approved	Allen	10/10/20	X.XXX ±0.15		ROHS COMPLIANT 2011/65/EU Deca-BDEV	
						Sheet No. 2/3



SEE DETAIL X



	REEL	CARTON
QUANTITY (PCS)	1400	14000

Part Number			Product Description		
PTCFW-H22A-032			USB 2.0 Type C Receptacle, Horizontal, SMT, Mid Mount, 1.0mm Offset, 16 Pin		
DWG.No.	P-TCF-044		Tolerances Unspecified		Units: Metric(mm)
Revision	A0		X.X ±0.35	X° ±5°	
Designed	Lee	10/10/20	X.XX ±0.25	X.X° ±2°	
Approved	Allen	10/10/20	X.XXX ±0.15		

WF
Connecting the Future

www.szywf.com.cn
www.szywf.cn

Sheet No. 3/3