





公差参数

Poles	Dim	Dim. P	Dim. L
2-6P		±0.10	±0.20
7-12P		±0.20	±0.30
13-18P		±0.25	±0.40
19-24P		±0.30	±0.50



材料及电镀

- ①. 螺 丝: M2.5, 钢, 镀锌, 一字槽
- ②. 塑件主体: PA66, UL94V-0
- ③. 焊 脚: 黄铜, 镀镍
- ④. 方 盒: 黄铜, 镀镍

电气性能

额定电压: 300V
额定电流: 15A
接触电阻: 20mΩ (Max)
绝缘电阻: 500MΩ \DC500V
耐 电 压: AC2000V\1Min
使用线径: 30-14AWG 2.5mm²

机械性能

温度范围: -40℃ ~ +105℃
瞬时温度: +250℃ 5秒
扭 力: 0.4Nm (3.54Lbin)
剥线长度: 6-7mm

Ordering Information

HC128 * - * - NP - * - *

Type: 1=直针, 2=弯针
PITCH: 5.00=5mm
No. of Pins: 2-24Pin
Colour: V=Green, L=Bluc, O=Orange, R=Red, S=Black, GR=Gray
Pin Marking: 十字=Slotted, 一字=Phillips (十字螺丝)

			GENERAL TOLERANCE		制 图 DRAWING		 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD					
			DIM	TOL	审 核 CHECK							
					X.X	±0.50	批 准 APPROVAL		产品名称 TITLE	5.00 单排 螺丝式 接线端子 直针 (一字螺丝)	版 本 REV.	A
			1	初版发行		X.XX	±0.30	比 例 SCALE		产品料号 PART NO.	HC128V-5.00-NP-X	单 位 UNITS
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX	±0.10	投 影 Projection				材料 MATERIAL	页 次 SHEET	1/1	
			Angle	±3.0°								