

符合RoHS环保要求

项目 Mapx	设计内容 Modification	日期 Date	修改人 Draw	核准 Approve
△				

规格说明:Specifications:

电气特性:Electrical:

- 1.额定电流: Current Rating
1.5A/contact terminal
- 2.额定电压: Voltage Rating
30V DC
- 3.接触电阻: Contact Resistance
30 milliohms MAX
- 4.耐电压: Dielectric Withstanding Voitage:
500 V AC AT Sea Level
- 5.绝缘电阻: Lnsulation Resistance:
1000MEGA ohms MIN

- 1.插拔力: Cnector Mate and Unmate Force
Mate force:3.57kgf(MAX)
Unmate force:1.02kgf(MIN)
- 2.端子保持力: Terminal Retenion
1.0kgf(MIN)

- 1.塑胶:Housing:
Hing Temperature Thernmaplastics,

- 2.端子:Contact:Copper Alloy C2680

- 3.外壳:Shell: Stainless steel 201


电镀:Finish:

- 1.端子:Contact: Plated Gold in Mating Area;
Tin On Solder Talls



端子四周镀60U”(MIN)–100U锡,”镀金1U”

- 2.外壳:Shell:
外壳插脚镀80U”(MIN)镍

Nickel Plating



RECOMMENDED PCB LAYOUT



PIN NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND
5	SSRX-
6	SSRX+
7	GND
8	SSTX-
9	SSTX+
Shell	Shield

成品图 MANUFACTURE DWG	
公差一览表 TOLERANCE UNLESS OTHERWISE	
.X±0.15	.X±5°
.XX±0.05	.X±2°
XXX±0.02	.XX±1°

东莞市文章济美电子有限公司

DATE	DATE	UNIT	MM	DRAWING	DRAWING	DWG NO.	5001-USB1504020-081B
CHECKED	CHECKED	比例 SCALE	1:1	设计 DESIGN	JUFU	品名 NAME	侧插3.0卷边
APPROVE	APPROVE	角法 VIEW				版本 VER	VER 页数 SHEET 002