




AN B 0 200 1 -1 2 5  
AN=ANTENNA  
B=BOARD END  
0=STANDARD HEIGHT  
200=OUTER DIAMETER  
GROUND CONTACT PLATING  
1=Au 1u" Min.  
WITH CHAMFER (5000PCS/R)  
2=STREAM CODE  
1=1st GENERATION



P.C.B DIMENSION (TOP VIEW)  
(TOLERANCE ±0.05)

- NOTES:  
1. FREQUENCY RANGE:  
DC TO 6GHZ (VSWR: 1.3MAX AT 0.1~3GHZ,  
1.4MAX AT 3~6GHZ)  
2. CHARACTERISTIC IMPEDANCE:  
50Ω(NOMINAL);  
3. TEMPERATURE: -40°C TO +90°C;  
4. RATED VOLTAGE: 60VAC;  
5. CONTACT RESISTANCE:  
20mΩ MAX.(SIGNAL CONTACT)  
20mΩ MAX.(GROUND CONTACT)  
6. WITHSTAND VOLTAGE: 200VAC FOR 1  
MINUTE MIN;  
7. INSULATION RESISTANCE: 500MΩ MIN. AT  
100VDC;  
8. THIS COMPONENT IS HALOGEN FREE.

|      |                |      |               |                                    |
|------|----------------|------|---------------|------------------------------------|
| 3    | GROUND CONTACT | 1    | COPPER ALLOY  | GOLD FLASH OVER NI PLATED OVERALL. |
| 2    | SIGNAL CONTACT | 1    | COPPER ALLOY  | GOLD FLASH OVER NI PLATED OVERALL. |
| 1    | HOUSING        | 1    | THERMOPLASTIC | UL94V-0                            |
| ITEM | NAME           | Q'TY | MATERIAL      | FINISH                             |

|      |    |      |       |             |    |     |     |              |              |                   |
|------|----|------|-------|-------------|----|-----|-----|--------------|--------------|-------------------|
| 更改记录 | 标记 | 变更内容 | 签名/日期 | 未注公差        | 单位 | mm  | 标准化 | 签名/日期        | 品名           | IPEX一代板端 3PIN镀金   |
|      |    |      |       | X.X ±0.30   | 版本 | A   | 编制  | 周少华 21.09.25 | 图号           | ZJLQ-ANB02001-125 |
|      |    |      |       | X.XX ±0.20  | 比例 | 1:1 | 审核  | 赵先礼 21.09.25 | 浙江领强电子科技有限公司 |                   |
|      |    |      |       | X.XXX ±0.10 | 投影 |     | 批准  | 田泽民 21.09.25 |              |                   |
|      |    |      |       | Angle ±3.0° | 页次 | 1/1 |     |              |              |                   |