



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.07.29	阿树


A



3D图示（参考）



04P~10P



02P~03P

■SPECIFICATIONS




- Voltage rating:250V AC/DC
- Current rating:7A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:−40°C~+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤20mΩ

PART NO.:


X9396 W V-02-N0 SN
① ② ③ ④ ⑤ ⑥

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:V-Stright 180°
- ④Row No.Pin No:XX-02~15Pin
- ⑤Material:N0-PA66 UL94V-0
- ⑥Planting: SN-Bright tin plating



B



C



PCB LAYOUT



Poles	Dimensions(mm)	
	A	B
02	3.96	7.92
03	7.92	11.88
04	11.88	15.84
05	15.84	19.80
06	19.80	23.76
07	23.76	27.72
08	27.72	31.68
09	31.68	35.64
10	35.64	39.60

D

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	3.96mm Crimp Style Connectors
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4
PART NO		MODEL TYPE:	
Material		PART NO.:	
Material(Pin)		X9396WV-02-N0SN	
Finish		DWG NO.:	
Suitable XKB Housing			