





	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
AO	N/A		INITIAL RELEASE	2024.02.29	




Specifications (规格):

1. Voltage rating(额定电压):50V AC DC
2. Current rating(额定电流):2.4A AC/DC
3. Withstanding voltage(耐压值): $\geq 500\text{V AC/minute}$
4. Insulation resistance(绝缘电阻): $500\text{M}\Omega$ Min
5. Contact resistance(绝缘电阻): $20\text{m}\Omega$ Max
6. Temperature range(使用温度): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$



X1502 W R-05 K-NO SN
 ① ② ③ ④ ⑤ ⑥ ⑦


- ① Series No
- ② Category:W-Wafer
- ③ Welding Board Angle:R-Straight 90°
- ④ Row No-Pin: XX-02P~15P
- ⑤ Plug The Pin&Special NO:K-Kink
- ⑥ Material:NO-PA66 UL94V-0
- ⑦ Plating:SN-Bright Tin Plated



NUMBER OF POSITIONS	DIM.A	DIM.B	DIM.C	NUMBER OF POSITIONS	DIM.A	DIM.B	DIM.C
02	1.50	4.50	3.70	09	12.00	15.00	14.20
03	3.00	6.00	5.20	10	13.50	16.50	15.70
04	4.50	7.50	6.70	11	15.00	18.00	17.20
05	6.00	9.00	8.20	12	16.50	19.50	18.70
06	7.50	10.50	9.70	13	18.00	21.00	20.20
07	9.00	12.00	11.20	14	19.50	22.50	21.70
08	10.50	13.50	12.70	15	21.00	24.00	23.20

X1502WR-05K-N0SN	PA66 UL 94V-0	BRASS	TIN-PLATED	X1502H
PART NO.	MATERIAL	MATERIAL(PIN)	FINISH(PIN)	Suitable XKB Terminal

ANGLAR	$\pm 5^{\circ}$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 菴	VIEW: 	MODEL TYPE: 1.50mm Crimp Style Connector		
CHECKED		UNIT: mm/in	PART NO.: X1502WR-05K-N0SN		
APPROVED		SIZE: A4	DWG NO.: X-X1502WR-05K-N0SN		
PRECISION CO.,LIMITED			SCALE N/A	PAGE 1 / 1	REVISION A0