





P.C.B LAYOUT

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:300V AC/minute

耐受电压: 300V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥500MΩ

绝缘电阻: ≥500MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

Material:PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category:1U"Gold

镀层: 1U"Gold

Reflow soldering temperature:260±5℃, 10S

回流焊温度: 260±5℃, 10S

X1311 W V S - 10 J - C40 D42 R2  
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- 1.Series No.
- 2.Category:W-Water
- 3.Welding Board Angle:V-Stright 180°
- 4.Welding Way S-SMT
- 5.Row No -Pin No:XX Pin
- 6.Plastic height:J=1.0mm
- 7.Pin length: C=4.0mm
- 8.Pin length:D=4.2mm
- 9.Type:X-R1;R2

|                       |          |               |                     |
|-----------------------|----------|---------------|---------------------|
| X1311WVS-10J-C40D42R2 | PA6T     | Brass         | X1311F              |
| PART NO               | Material | Material(Pin) | Suitable XKB Female |

|                                      |             |                                  |
|--------------------------------------|-------------|----------------------------------|
| DSND                                 | SCALE: N/A  | MODEL TYPE:                      |
| DWN                                  | VIEW:       | 1.27mm BTB Connector             |
| CHKD                                 | UNIT: mm/in | PART NO.: X1311WVS-10J-C40D42R2  |
| APPD                                 | SIZE: A4    | DWG NO.: X-X1311WVS-10J-C40D42R2 |
| XKB INDUSTRIAL PRECISION CO.,LIMITED |             | WEIGHT                           |
|                                      |             | SHEET 1/1                        |
|                                      |             | REVISION A0                      |

|                                               |             |      |         |          |                        |      |
|-----------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                               |             |      |         |          | ANGLAR                 | ±5°  |
| Δx                                            |             |      |         |          | L≤ 4                   | ±0.2 |
| Δx                                            |             |      |         |          | 4<L≤ 16                | ±0.3 |
| Δx                                            |             |      |         |          | 16<L≤ 63               | ±0.4 |
| MARK                                          | DESCRIPTION | DATE | REVISED | APPROVED | L> 63                  | ±0.5 |
| REVISIONS                                     |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |             |      |         |          |                        |      |

XKB