








REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	N/A		产品尺寸变更, 图面升级整理图面	2024.08.24	阿树



PCB LAYOUT



SCHEMATIC

- 1.CONTACT CURRENT RATING: 1A.
- 2.CONTACT RESISTANCE: 50 mΩ MAX.
- 3.INSULATION RESISTANCE: 1000Ω MIN.;
- 4.DIELECTRIC WITHSTANDING:500V AC MIN.;
- 5.DURABILITY: 5,000 CYCLES MIN.;
- 6.CONNECTOR MATING FORCES:30NMAX.,
- 7.CONNECTOR UNMATING FORCES:3N MIN.

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEWS	VIEW:	MODEL TYPE:	3.50mm PHONE JACK
CHECKED		UNIT:	mm/in	PART NO.:	PJ-3420-A-SMT
APPROVED		SIZE:	A4	DWG NO.:	X-PJ-3420-A-SMT

SCALE	PAGE	REVISION
N/A	1/1	A1