



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A2	N/A		图面修正，图面升级整理图面	2024.12.2	阿树
A3	N/A		系列图拆分	2025.03.31	阿树



Specifications:

规格:

电气额定值Electrical Rating: 16A 250V AC

环境温度Ambient temperature:T125

电气寿命Electrical lifetime:5E4 cycles

动作力Operating force:1.8±0.8N

自由位置Free position:21.7±1mm


动作位置Operating position: 20.7±1mm

接触电阻Contact Resistance:≤50mΩ


耐压(Withstand Voltage): 端与端500V/60S/5mA,
端与壳1500V/60S/5mA。

绝缘电阻(Insulation Resistance): ≥100MΩ (Test Voltage 500VDC)

电路简图



端子尺寸:



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: MICRO SWITCH
CHECKED		UNIT: mm/in	PART NO.: DV-16-148GN-1
APPROVED		SIZE: A4	DWG NO.: