







Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:800V AC/minute

耐受电压: 800V AC/分钟

Temperature range:-25℃-+85℃

温度范围: -25℃-+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ

After environmental testing:≤20mΩ

环境测试后: ≤20兆欧

X2026 W V X-2x02A- N0 SN

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1.Series No

2.Category:W-WAFER

3.Welding Board Angle:V-Straight 180°

4.Welding Way:Blank-DIP

5.Row No-Pin No:2xXX-2x02P~2x22P

6.Plug the Pin&Special N0:

A-With Lock on both side

7.Material:6T-PA6T 94V-0;N0-PA66 94V-0

8.Plating Category:SN-Bright Tin Plating

9.Color:Blank-Natural Color

poles	Dimensions(m m)		poles	Dimensions(m m)		Poles	Dimensions(m m)		Poles	Dimensions(m m)	
	A	B		A	B		A	B		A	B
2x02	2.00	8.00	2x09	16.00	22.00	2x16	30.00	36.00	2x23	44.00	50.00
2x03	4.00	10.00	2x10	18.00	24.00	2x17	32.00	38.00	2x24	46.00	52.00
2x04	6.00	12.00	2x11	20.00	26.00	2x18	34.00	40.00	2x25	48.00	54.00
2x05	8.00	14.00	2x12	22.00	28.00	2x19	36.00	42.00			
2x06	10.00	16.00	2x13	24.00	30.00	2x20	38.00	44.00			
2x07	12.00	18.00	2x14	26.00	32.00	2x21	40.00	46.00			
2x08	14.00	20.00	2x15	28.00	34.00	2x22	42.00	48.00			

X2026WV-2x02A-6TS N	PA6T UL 94V-0	Brass	Tin-Plated	X2026H-A
X2026WV-2x02A-N0 SN	PA66 UL 94V-0			X2026H-A
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Housing

Wire to board connector

						DSND		DATE		SCALE: N/A	MODEL TYPE:
						DWN		DATE		VIEW: 	2.00mm Crimp Style Connectors
						CHKD		DATE		UNIT: mm/in	PART NO.:
						APPD		DATE		SIZE: A4	DWG NO.:
											X2026WV-2x02A-N0SN
											X-X2026WV-2x02A-N0SN
											REVISION
											1.0g
											1/1
											A0

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED

units:	mm
tolerance:	
X.X	±0.2mm
X.XX	±0.1mm
X.XXX	±0.05mm

ΔX					
ΔX					
ΔX					
MARK	DESCRIPTION	DATE	REVISED	APPROVED	

REVISIONS

UNSPECIFIED TOLERANCES