






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.09.05	阿树

A


B

C

D



PCB LAYOUT PLAN



PAPT NO	L
SS-1400S-L1	1.5
SS-1400S-L2	2.0
SS-1400S-L3	2.5

- Specifications (规格):
- 1.Voltage rating (额定电压):DC 12V
 - 2.Current rating (额定电流):0.5A AC/DC
 - 3.Withstanding voltage (耐压值):≥100V AC(50-60Hz)/minute
 - 4.Insulation resistance (绝缘电阻):≥100MΩ Min
 - 5.Mating cycles (使用寿命): 10,000 cycles Min
 - 6.Operating Force (动作力): 250gf±100gf
 - 7.Temperature range (使用温度):-10℃~+60℃

E	Cover	SUS	silvery white	1
D	Contact reeds	Phosphor bronze silver-plated	silvery white Silver-inlaid	2
C	Handle	PA46	Black	1
B	Cards	Brass	silvery white silver-plated	1
A	Housing	LCP	Gray-black	1
ITEM	PAPT NAME	MATERIAL	FLASH/COLOR	QTY

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE:	SLIDE SWITCH
PART NO.:	SS-1400S-L2
DWG NO.:	X-SS-1400S-L2

SCALE	PAGE	REVISION
N/A	2/2	A1

A

B

C

D