






14P-64P 双槽



TYPE 3



Y型端子



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ MAX

接触电阻: ≤20mΩ MAX

X9555 H4 -2x10 - PT 01

① ② ③ ④ ⑤ ⑥

1.Series No

2.Category:H4-HSG with TYPE 3

3.Row No-Pin No:2xXX-2x03P~2x32P

4.Special:NO:X Type A or Type B and Type C


Blank-conventional product

6.Material:PT-PBT UL94V-0

7.Plating:V01-Gold Flash


X9555H4-2x10-PTV01	PBT	BRASS	Gold Flash	X9555WV-2xXX	XPD1.27-A28PXX-IDC	X9555H-2xXXA
				X9555WR-2xXX		X9555H-2xXXB
				X9555WVS-2xXX		X9555H-2xXXC
				X9555WV-2xXX		X9555H-2xXXA
				X9555WR-2xXX		X9555H-2xXXB
X9555H4-2x10-PTV01				X9555WVS-2xXX		X9555H-2xXXC
PART NO	Material	Material(pin)	Finish(pin)	Suitable XXB Wire	Suitable XXB flat cable	Suitable XXB DIP

NUMBER OF POSITIONS	DIMENSION			NUMBER OF POSITIONS	DIMENSION		
	A	B	C		A	B	C
06	12.32	5.08	3.8	26	37.72	30.48	3.8
08	14.86	7.62	3.8	30	42.80	35.56	3.8
10	17.40	10.16	3.8	34	47.88	40.64	3.8
12	19.94	12.70	3.8	36	50.42	43.18	3.8
14	22.48	15.24	3.8	40	55.50	48.26	3.8
16	25.02	17.78	3.8	44	60.58	53.34	3.8
18	27.56	20.32	3.8	50	68.20	60.96	3.8
20	30.10	22.86	3.8	60	80.90	73.66	3.8
22	32.64	25.40	3.8	64	85.98	78.74	3.8
24	35.18	27.94	3.8				




6P 小鼻/无槽

TYPE C




6P 大鼻/无槽

TYPE A




8P 大鼻/无槽

TYPE A




6P 小鼻/单槽

TYPE B



8P 小鼻/单槽

TYPE B



10P-12P 单槽

Blank

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
DESCRIPTION					DATE	REVISED
REVISIONS					APPROVED	UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.54mm IDC		
DWN		VIEW:	PART NO.: X9555H4-2x10-PTV01		
CHKD		UNIT: mm/in	DWG NO.: X-X9555H4-2x10-PTV01		
APPD		SIZE: A4	WEIGHT	SHEET 1/1	REVISION A0