



Specifications:  
Voltage rating:250V AC/DC  
Current rating:2A AC/DC  
Withstanding voltage:800V AC/minute  
Temperature range:-40℃~+85℃  
Insulation resistance:≥1000MΩ  
Contact resistance:≤20mΩ





X2016 H M - 06 - N0

①      ②③      ④      ⑤

1.Series No  
2.Category:H-Housing  
3.M-Male  
4.Row No.Pin No:XX-02~16P  
5.Material:N0-PA66 UL 94V-0

| POLES | A     | B     | C     |
|-------|-------|-------|-------|
| 2     | 2.00  | 4.60  | 5.80  |
| 3     | 4.00  | 6.60  | 7.80  |
| 4     | 6.00  | 8.60  | 9.80  |
| 5     | 8.00  | 10.60 | 11.80 |
| 6     | 10.00 | 12.60 | 13.80 |
| 7     | 12.00 | 14.60 | 15.80 |
| 8     | 14.00 | 16.60 | 17.80 |
| 9     | 16.00 | 18.60 | 19.80 |
| 10    | 18.00 | 20.60 | 21.80 |
| 11    | 20.00 | 22.60 | 23.80 |
| 12    | 22.00 | 24.60 | 25.80 |
| 13    | 24.00 | 26.60 | 27.80 |
| 14    | 26.00 | 28.60 | 29.80 |
| 15    | 28.00 | 30.60 | 31.80 |
| 16    | 30.00 | 32.60 | 33.80 |



|               |               |                          |                                  |
|---------------|---------------|--------------------------|----------------------------------|
| X2016HM-06-N0 | PA66 UL 94V-0 | X2016TF                  | X2016W X2016HF                   |
| PARY N0       | Matrial       | Suitable XKB<br>Terminal | Suitable XKB Wafer or<br>Housing |

|                       |  |                                                                                             |                                             |       |          |
|-----------------------|--|---------------------------------------------------------------------------------------------|---------------------------------------------|-------|----------|
| DSND                  |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>2.0mm Crimp Style Connectors |       |          |
| DWN                   |  | VIEW:  | PART NO.:<br>X2016HM-06-N0                  |       |          |
| CHKD                  |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-X2016HM-06-N0                 |       |          |
| APPD                  |  | SIZE: A4                                                                                    |                                             |       |          |
| PRECISION CO.,LIMITED |  |                                                                                             | WEIGHT                                      | SHEET | REVISION |
|                       |  |                                                                                             |                                             | 1/1   | A0       |

|                                               |             |      |         |          |                        |      |
|-----------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                               |             |      |         |          | ANGLAR                 | ±5°  |
| Δx                                            |             |      |         |          | L ≤ 4                  | ±0.2 |
| Δx                                            |             |      |         |          | 4 < L ≤ 16             | ±0.3 |
| Δx                                            |             |      |         |          | 16 < L ≤ 63            | ±0.4 |
| MARK                                          | DESCRIPTION | DATE | REVISED | APPROVED | L > 63                 | ±0.5 |
| REVISIONS                                     |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com www.helloxkb.cn www.xk-da.cn |             |      |         |          |                        |      |

# XKIE

XKB INDUSTRIAL PRECISION CO.,LIMITED