








## ■ Specifications :

- Voltage rating: 50 V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance:  $\geq 500M\Omega$
- Contact resistance:  $\leq 20m\Omega$
- After environmental testing :  $\leq 30m\Omega$

X1502 W V S-06-9T SN

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category : W-WAFER
- ③ Welding Board Angle : V-Straight 180°
- ④ Welding Way:S-SMT
- ⑤ Row No.-Pin No.: XX-02P~15P
- ⑥ Material : 9T-PA9T;6T-PA6T;LP-LCP 94V-0
- ⑦ Plating Category: Sn-Bright Tin Plating

| Poles | Dimensions(mm) |       |       | Poles | Dimensions(mm) |       |       |
|-------|----------------|-------|-------|-------|----------------|-------|-------|
|       | A              | B     | C     |       | A              | B     | C     |
| 02    | 1.50           | 6.00  | 3.60  | 09    | 12.00          | 16.50 | 14.10 |
| 03    | 3.00           | 7.50  | 5.10  | 10    | 13.50          | 18.00 | 15.60 |
| 04    | 4.50           | 9.00  | 6.60  | 11    | 15.00          | 19.50 | 17.10 |
| 05    | 6.00           | 10.50 | 8.10  | 12    | 16.50          | 21.00 | 18.60 |
| 06    | 7.50           | 12.00 | 9.60  | 13    | 18.00          | 22.50 | 20.10 |
| 07    | 9.00           | 13.50 | 11.10 | 14    | 19.50          | 24.00 | 21.60 |
| 08    | 10.50          | 15.00 | 12.60 | 15    | 21.00          | 25.50 | 23.10 |

|                    |                              |               |             |                       |
|--------------------|------------------------------|---------------|-------------|-----------------------|
| X1502WVS-06HF-LPSW | LCP UL 94V-0<br>Halogen Free | Brass         | Tin-Plated  | X1502T                |
| X1502WVS-06-6TSN   | PA6T UL 94V-0                |               |             |                       |
| X1502WVS-06-9TSN   | PA9T UL 94V-0                |               |             |                       |
| PART NO            | Material                     | Material(pin) | Finish(pin) | Suitable XKB Terminal |

|  |  |  |  |  |  |                                      |  |      |  |             |                                             |       |          |
|--|--|--|--|--|--|--------------------------------------|--|------|--|-------------|---------------------------------------------|-------|----------|
|  |  |  |  |  |  | DSND                                 |  | DATE |  | SCALE: N/A  | MODEL TYPE:<br>1.5mm Crimp Style Connectors |       |          |
|  |  |  |  |  |  | DWN                                  |  | DATE |  | VIEW:       | PART NO.:<br>X1502WVS-06-9TSN               |       |          |
|  |  |  |  |  |  | CHKD                                 |  | DATE |  | UNIT: mm/in | DWG NO.:<br>X-X1502WVS-06-9TSN              |       |          |
|  |  |  |  |  |  | APPD                                 |  | DATE |  | SIZE: A4    |                                             |       |          |
|  |  |  |  |  |  | XKB INDUSTRIAL PRECISION CO.,LIMITED |  |      |  |             | WEIGHT                                      | SHEET | REVISION |
|  |  |  |  |  |  |                                      |  |      |  |             | 1.0g                                        | 1/1   | A0       |

|                                               |  |  |  |  |         |                        |
|-----------------------------------------------|--|--|--|--|---------|------------------------|
|                                               |  |  |  |  | ANGLAR  | ±5°                    |
| ΔX                                            |  |  |  |  | L≤4     | ±0.2                   |
| ΔX                                            |  |  |  |  | 4<L≤16  | ±0.3                   |
| ΔX                                            |  |  |  |  | 16<L≤63 | ±0.4                   |
| MARK                                          |  |  |  |  | L>63    | ±0.5                   |
| REVISIONS                                     |  |  |  |  |         | UNSPECIFIED TOLERANCES |
| www.xk-dg.cn www.helloxkb.com www.helloxkb.cn |  |  |  |  |         |                        |