






Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1 500V AC/ 分钟

Temperature range:-25 ℃ -+85℃

温度范围: -25℃ -+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

After environmental testing:≤30mΩ

环境测试后: ≤30 兆欧

X9555 H -2x05 E2-PT

① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:H-HSG
- 3.Welding Board Angle:Blank-ordinary
- 4.Row No-Pin No:2xXX-2x02P~2x32P
- 5.Special No:
E2-With single convex point,Thickness=5.05mm
- 6.Material:PT-PBT 94V-0
- 6.Color:Blank-Natural Color

poles	Dimensions(mm)		poles	Dimensions(mm)		poles	Dimensions(mm)	
	A	B		A	B		A	B
2x02	2.54	5.08	2x13	30.48	33.02	2x24	58.42	60.96
2x03	5.08	7.62	2x14	33.02	35.56	2x25	60.96	63.50
2x04	7.62	10.16	2x15	35.56	38.10	2x26	63.50	66.04
2x05	10.16	12.70	2x16	38.10	40.64	2x27	66.04	68.58
2x06	12.70	15.24	2x17	40.64	43.18	2x28	68.58	71.12
2x07	15.24	17.78	2x18	43.18	45.72	2x29	71.12	73.66
2x08	17.78	20.32	2x19	45.72	48.26	2x30	73.66	76.20
2x09	20.32	22.86	2x20	48.26	50.80	2x31	76.20	78.74
2x10	22.86	25.40	2x21	50.08	53.34	2x32	78.74	81.28
2x11	25.40	27.94	2x22	53.34	55.88			
2x12	27.94	30.48	2x23	55.88	58.42			

X9555H-2x05E2-PT	PBT UL 94V-0	X9555T-A	X9555W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Wafer

						DSND		DATE		SCALE: N/A	MODEL TYPE: 2.54mm Crimp Style Connectors		
					units: mm	DWN		DATE		VIEW: 	PART NO.: X9555H-2x05E2-PT		
Δ x					tolerance: X.X ±0.2mm	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X9555H-2x05E2-PT		
Δ x					X.XX ±0.1mm	APPD		DATE		SIZE: A4			
Δ x					X.XXX ±0.05mm								
MARK	DESCRIPTION			DATE	REVISED	APPROVED							
REVISIONS						UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn											WEIGHT 1.0g	SHEET 1/1	REVISION A0