





| REVISIONS |         |          |             |            |        |
|-----------|---------|----------|-------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION | DATE       | DESIGN |
| A1        | N/A     |          | 图片面升级整理图面   | 2024.07.26 | 阿 树    |
|           |         |          |             |            |        |



SS13E05-L12

L(MM)  
2~12



|                    |             |
|--------------------|-------------|
| RATING             | 0.3A 50V DC |
| CIRCUIT            | 1P3T        |
| CONTACT RESISTANCE | 100MΩ MAX   |
| TRAVEL             | 2.5MM       |
| OPERATING FORCE    | 250±100gf   |
| OPERATING LIFE     | 10000       |

|      |           |        |     |          |           |  |
|------|-----------|--------|-----|----------|-----------|--|
| 4    | Terminal  | —      | 4   | SUS      |           |  |
| 3    | Base      | —      | 1   | SUS      |           |  |
| 2    | Cover     | —      | 1   | SUS      |           |  |
| 1    | Keystake  | —      | 1   | PA66     |           |  |
| ITEM | PAPT NAME | TER.NO | QTY | MATERIAL | FINISHING |  |

|                        |       |
|------------------------|-------|
| ANGULAR                | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



|                       |     |             |                                                                                       |                             |      |          |
|-----------------------|-----|-------------|---------------------------------------------------------------------------------------|-----------------------------|------|----------|
| DESIGN                | 阿 树 | VIEW:       |  | MODEL TYPE:<br>SLIDE SWITCH |      |          |
| CHECKED               |     | UNIT: mm/in |                                                                                       | PART NO.:<br>SS13E05L12     |      |          |
| APPROVED              |     | SIZE: A4    |                                                                                       | DWG NO.:<br>X-SS13E05L12    |      |          |
| PRECISION CO.,LIMITED |     |             |                                                                                       | SCALE                       | PAGE | REVISION |
|                       |     |             |                                                                                       | N/A                         | 1/1  | A1       |