





PCB Layout



Current rating:25A AC/DC
 额定电流: 25A AC/DC
 Temperature range:-40℃~+125℃
 温度范围: -40℃~+125℃

K 966140 W R - 3x02 - PT SW
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:W-Wafer
- 4.Welding Board Rangle:R-Stright 90°
- 5.Row No.Pin No:3xXX-3x02~3x07 Pin
- 6.Material:PT-PBT (Black)
- 7.Palting:SW-Matte Tin

Poles	Dimensions(mm)			
	A	B	C	D
3x02	5.00	11.60	17.50	20.00
3x03	10.00	16.60	22.50	25.00
3x04	15.00	21.60	27.50	30.00
3x05	20.00	26.60	32.50	35.00
3x06	25.00	31.60	37.50	40.00
3x07	30.00	36.60	42.50	45.00

K966140WR-3x02-PTSW	PBT	Brass	K966140WR
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 5.0mm Automobile connector
DWN		VIEW:	PART NO.: K966140WR-3x02-PTSW
CHKD		UNIT: mm/in	DWG NO.: X-K966140WR-3x02-PTSW
APPD		SIZE: A4	
			WEIGHT
			SHEET
			REVISION
			1/1
			A0

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dq.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED