



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.12.16	阿树


A




B



C



D



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	1.27mm BTB Style Connectors
CHECKED		UNIT:	mm/in	PART NO.:	X1270H-2x30A-PTAUSN
APPROVED		SIZE:	A4	DWG NO.:	

Voltage rating:50V AC/DC
额定电压:50V AC/DC
Current rating:0.5A
额定电流: 0.5A
Insulation resistance:1000MΩ Min
绝缘电阻: 1000MΩ Min
Withstanding voltage:≥300V AC/minute
耐压: ≥300VC/分钟
Temperature range:-45℃-+125℃
使用温度: -45℃-+125℃

PART NO.:

X1270 H-2x30 A-PT AUSN
① ② ③ ④ ⑤ ⑥

- ①Series No
- ②Category:H-HSG
- ③Row No-Pin No:2xXX-2x05P~2x50P
- ④A:1.27x2.54mm
- ⑤Material:PT-Nylon PBT UL94V-0
- ⑥Planting Category:AUSN-AUSN Plating

PINS	A	B	C
2x05P	11.25	8.35	5.08
2x07P	13.79	10.89	7.62
2x08P	15.06	12.12	8.89
2x10P	17.60	14.70	11.43
2x13P	21.41	18.51	15.24
2x15P	23.95	21.05	17.78
2x16P	25.22	22.32	19.05
2x17P	26.49	23.59	20.32
2x20P	30.30	27.40	24.13
2x25P	36.65	33.75	30.48
2x30P	43.00	40.10	36.83
2x34P	48.08	45.18	41.91
2x50P	68.40	65.50	62.23