


Specifications

Voltage Rating: 250VAC/DC
Current Rating: 3A AC/DC Withstanding
Voltage: 1500V AC/Minute
Insulation Resistance: 1000 Ω Min.
Temperature Range: -25°C ~ +85°C
Contact Resistance: 20m Ω Max
Material: PBT, UL94V-0
Color: Natural/Black
Q'ty/Bag: 1000PCS

X2530 H F-11-PT
① ② ③ ④ ⑤

Ordering Information & Dimensions

Poles	Dimensions (mm)				
	A	B	Poles	A	B
02	2.54	7.42	12	27.94	32.82
03	5.08	9.96	13	30.48	35.36
04	7.62	12.50	14	32.02	37.90
05	10.16	15.04	15	35.56	40.44
06	12.70	17.58	16	38.10	42.98
07	15.24	20.12	17	40.64	45.52
08	17.48	22.66	18	43.18	48.06
09	20.32	25.20	19	45.72	50.06
10	22.86	27.74	20	48.26	43.14
11	25.40	30.28			

1. Series No.
2. Category: H-Housing
3. Housing Type: M-Male Housing
4. Pin No.: 03-03PIN.....20-20PIN
5. Material: PT-PBT, UL94V-0

X2530HF-11-PT	PBT UL94V-0	X2530TM	X2530W
X2530HF-2x11-PT			
PART NO	Material	Suitable XKB Housing	Suitable XKB Wafer

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO., LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.54mm Crimp Style Connector		
}	DWN	VIEW: 	PART NO.: X2530HF-11-PT		
	CHKD	UNIT: mm/in	DWG NO.: X-X2530HF-11-PT		
	APPD	SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET 1/1	REVISION A0