





Code-x	H	Code-x	H
A	4.30	O	11.00
B	4.50	P	11.50
C	5.00	Q	12.00
D	5.50	R	12.50
E	6.00	S	13.00
F	6.50	T	13.50
G	7.00	U	14.00
H	7.50	V	15.00
I	8.00	W	15.50
J	8.50	X	16.00
K	9.00	Y	17.00
L	9.50	Z	18.00
M	10.00	19	19.00
N	10.50		



SPECIFICATION

Contact Rating:	50mA, 12V DC
Contact Resistance:	100m Ω max
Insulation Resistance:	100M Ω min. 500V DC
Dielectric Strength:	250V AC/1minute
Travel:	0.25mm
Operating Temp:	-30 $^{\circ}$ C~+85 $^{\circ}$ C
Storage Temp:	-30 $^{\circ}$ C~+80 $^{\circ}$ C

PAPT NO	TS-1103S-B-A
Operating Force	B:160gf C:260gf
Height	Code-x



P.C.B MOUNTING PATTERN DIMENSION
The following soldering patterns are recommended for reflow soldering

⑤	Terminal	4	Brass (0.30t)	Plating silvering	
④	Contact	1	F.ag/SUS	Natural	
③	Base	1	Pa46		
②	Cover	1	Spcc	Plating Nickel	
①	Keystake	1	Pa46		
ITEM	PAPT	NAMF	QTY	MATERIAL	FINISHING

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	TACT SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	TS-1103S-B-A
APPROVED		SIZE:	A4	DWG NO.:	TS-1103S-B-A
PRECISION CO., LIMITED				SCALE	PAGE
				N/A	1/1
				REVISION	A1