




Specifications:

规格:

Voltage rating:150V AC/DC

额定电压: 150V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-25°C-+85°C

温度范围: -25℃-+85℃

Insulation resistance: 500MΩ min

绝缘电阻: 500MΩ Min

Contact resistance:30mΩ Max

接触电阻: 30mΩ Max

X9862 W V S -06 A -6T SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1.Series No

2. Category :W-Wafer

3.Welding Board Angle:V-Straight 180°


4. Welding Way: S-SMT

5.Row No.Pin No:XX-02P-30P

6.Special No: A-With Lock

7.Material: 6T-PA6T UL94V-0 Beige

8.Plating:SN- Tin Plating



P.C.B LAYOUT

Poles	Dimensions(mm)	
	A	B
02	1.25	7.45
03	2.50	8.70
04	3.75	9.95
05	5.00	11.20
06	6.25	12.45
07	7.50	13.70
08	8.75	14.95
09	10.00	16.20
10	11.25	17.45
11	12.50	18.70
12	13.75	19.95
13	15.00	21.20
14	16.25	22.45
15	17.50	23.70
20	23.75	29.95
25	25.00	36.20
30	36.25	42.45

X9862WVS-06A-6TSN	PA6T	Brass	X9862H-A
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector
DWN		VIEW: 	PART NO.: X9862WVS-06A-6TSN
CHKD		UNIT: mm/in	DWG NO.: X-X9862WVS-06A-6TSN
APPD		SIZE: A4	

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0