


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A2	N/A		PIN	2024.12.10	
A3	N/A			2025.09.05	

- Specifications:
- 1.Voltage rating:250V AC/DC
250V AC/DC
 - 2.Current rating:3A AC/DC
:3A AC/DC
 - 3.Withstanding voltage:500V AC/minute
:500V AC/
 - 4.Temperature range:-55 ~+105
:-55 ~+105
 - 5.Insulation resistance:≥1000MΩ
:≥1000MΩ
 - 6.Contact resistance:≤30mΩ
:≤30mΩ
 - 7.Rubber core:PBT UL94V-0
PBT UL94V-0
 - 8.The iron shell:SPCC-SD Nivkel Plating/Tin Plating/Gold Plating
SPCC-SD / /
 - 9.Terminal:Copper alloy




PART NO.:

X04 26 W I Z W 1

Series No
Row No-Pin No 26Pin
Welding Board Angle:W-Male
T:Tradutonal C:Car-pin
Planting Categoty:
1:1u 2:2u 3:3u 4:5u 5:15u 6:30u 7:AuSn
Color:B-Black W-White BL-Blue
1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4

	TYPE-1:	TYPE-2:	TYPE-3:	TYPE-4:

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	VIEW:	MODEL TYPE: D-SUB
CHECKED	UNIT: mm/in	PART NO.: X0426WT7W1
APPROVED	SIZE: A4	DWG NO.: