


Specifications

Voltage Rating: 250VAC/DC
 Current Rating: 3A AC/DC Withstanding
 Voltage: 1500V AC/Minute
 Insulation Resistance: 1000 Ω Min.
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 20m Ω Max
 Material: PBT, UL94V-0
 Color: Natural/Black
 Q'ty/Bag: 1000PCS

X2530 H F-09-PT
 ① ② ③ ④ ⑤

1. Series No.
2. Category: H-Housing
3. Housing Type: M-Male Housing,
4. Pin No.: 03-03PIN.....20-20PIN
5. Material: PT-PBT, UL94V-0

Ordering Information & Dimensions

Poles	Dimensions (mm)				
	A	B	Poles	A	B
02	2.54	7.42	12	27.94	32.82
03	5.08	9.96	13	30.48	35.36
04	7.62	12.50	14	32.02	37.90
05	10.16	15.04	15	35.56	40.44
06	12.70	17.58	16	38.10	42.98
07	15.24	20.12	17	40.64	45.52
08	17.48	22.66	18	43.18	48.06
09	20.32	25.20	19	45.72	50.06
10	22.86	27.74	20	48.26	43.14
11	25.40	30.28			

X2530HF-09-PT	PBT UL94V-0	X2530TM	X2530W
X2530HF-2x09-PT			
PART NO	Material	Suitable XKB Housing	Suitable XKB Wafer

					ANGULAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

DSND		SCALE: N/A	MODEL TYPE: 2.54mm Crimp Style Connector		
DWN		VIEW:	PART NO.: X2530HF-09-PT		
CHKD		UNIT: mm/in	DWG NO.: X-X2530HF-09-PT		
APPD		SIZE: A4			
			WEIGHT	SHEET	REVISION
				1/1	A0

XKB INDUSTRIAL PRECISION CO., LIMITED