





PCB LAYOUT



R1 TYPE



R2 TYPE

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

Material:PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category:1U"Gold

镀层: 1U"Gold

Wave soldering temperature:255±5℃, 10S

波峰焊温度: 255±5℃, 10S

X6511	W	R	22	H	C60	D30	R2
①	②	③	④	⑤	⑥	⑦	⑧

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:R-Stright 90°

4.Row No.Pin No:XX-02~40P

5.Plastic Height:H=2.5mm

6.Pin Length:C=6.0mm

7.Pin Length:D=3.0mm

8.Type: X-R1 ; R2

X6511WR-22H-C60D30R2	PA6T	Brass	X6511F
PART NO	Material	Material(Pin)	Suitable XKB Female

					ANGLAR	±5°
Δ x					L ≤ 4	±0.2
Δ x					4<L≤ 16	±0.3
Δ x					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-da.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	2.54mm BTB Connector
CHKD	UNIT: mm/in	PART NO.:
APPD	SIZE: A4	X6511WR-22H-C60D30R2
		DWG NO.:
		X-X6511WR-22H-C60D30R2
WEIGHT	SHEET	REVISION
	1/1	A0