










Specifications :

Voltage rating:100V AC / DC

Current rating: 2A AC / DC

Withstanding voltage: 500V AC/minute

Temperature range: -40°C~+85°C

Insulation resistance: ≥500MΩ

Contact resistance: ≤20mΩ

After environmental testing : ≤40mΩ

X1515 W R S-07-LP SW

① ② ③ ④ ⑤ ⑥ ⑦

① Series No.

② Category : W-WAFER

③ Welding Board Angle : R-Straight 90°

④ Welding Way:S-SMT

⑤ Row No.-Pin No.: XX-02P~15P

⑥ Material : LP-LCP 94V-0

⑦ Plating Category: SW-Matte Tin Plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	7.30	1.50	4.45	09	17.80	12.00	14.95
03	8.80	3.00	5.95	10	19.30	13.50	16.45
04	10.30	4.50	7.45	11	20.80	15.00	17.95
05	11.80	6.00	8.95	12	22.30	16.50	19.45
06	13.30	7.50	10.45	13	23.80	18.00	20.95
07	14.80	9.00	11.95	14	25.80	19.50	22.45
08	16.30	10.50	13.45	15	26.80	21.00	23.95

X1515WRS-07-LPSW	LCP UL 94V-0	Phosphor Bronze	X1515H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	1.5mm Crimp Style Connectors
CHKD	UNIT: mm/in	PART NO.:
APPD	SIZE: A4	X1515WRS-07-LPSW
		DWG NO.:
		X-X1515WRS-07-LPSW

ΔX	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					
ΔX					
ΔX					
MARK					

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0