



	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	桑 葚






规格 Specification:

- 1.额定值 Rating:3A 125/250VAC
- 2.接触电阻 Contact resistance: $\leq 30\text{ m}\Omega$
- 3.绝缘电阻 Insulation resistance: $\geq 100\text{ M}\Omega$ (DC500V/Min)
- 4.电气寿命 Electronics life: $> 10000\text{ cycles}$
- 5.操作力 Operation force: $500\pm 150\text{ gf}$
- 6.所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:


$$\frac{SS-X}{①} \quad \frac{03}{②} \quad \frac{22}{③} \quad \frac{S}{④} \quad \frac{G-9}{⑤} \quad \frac{R}{⑥} \quad \frac{4}{⑦} \quad \frac{B}{⑧} \quad \frac{B}{⑨} \quad \frac{B}{⑩} \quad \frac{B}{⑪}$$

- ① SS: XKB Vertical handle;
- ② Enclosure Material:
A—Metal case;
BLANK—Plastic case;
- ③ Current Rating: 03—3A;
- ④ Switch Circuit: 22—2P2T;
- ⑤ S: Wire bonding;
- ⑥ Handle Shape: G—Camber handle;
- ⑦ Handle Height: 3~15mm;
- ⑧ Enclosure Shape: R—Locking rings enclosure;
- ⑨ Terminal specs:
1: TYPE—1; 2: TYPE—2; 3: TYPE—3;
4: TYPE—4; 5: TYPE—5;
- ⑩ Handle Colour:
B—Black; W—White; R—Red
- ⑪ Housing Colour:
B—Black; W—White; R—Red



产品字码标识

ANGLAR	$\pm 5^{\circ}$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 葚	VIEW: 	MODEL TYPE: SLIDE SWITCH		
CHECKED		UNIT: mm/in	PART NO.: SS-0322SG-9R4BB		
APPROVED		SIZE: A4	DWG NO.: X-SS-0322SG-9R4BB		
PRECISION CO.,LIMITED			SCALE N/A	PAGE 1/1	REVISION A0

XKB INDUSTRIAL PRECISION CO.,LIMITED