






	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.07.01	阿树



MATING PLUG
Jack Insertion Depth: 8.3 mm



SCHEMATIC	
Model	DC-036A-2.5A
Center Pin	Ø2.0 mm Ø2.5 mm

Terminal 3	Brass	Tin
Terminal 2	Phosphor Bronze	Tin
Terminal 1	Brass	Tin
Center pin	Brass	Tin
Plastic	PBT	
Axis support	Brass	Tin
PART NAME	MATERIAL	PLATING

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XKLB 星城
Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: DC POWER JACK		
CHECKED		UNIT: mm/in	PART NO.: DC-036A-2.5A-2.5		
APPROVED		SIZE: A4	DWG NO.: DC-036A-2.5A-2.0		
PRECISION CO., LIMITED			SCALE	PAGE	REVISION
			N/A	1/1	A1

www.helloxkb.com	www.helloxkb.cn	www.xk-dg.cn
------------------	-----------------	--------------

XKB INDUSTRIAL PRECISION CO.,LIMITED