


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		料号说明pin数修改	2024.07.27	阿树
A2	N/A		独立各PIN数图纸, 增加开孔定位尺寸	2024.12.10	阿树

Specifications:

- 1.Voltage rating:250V AC/DC
额定电压: 250V AC/DC
- 2.Current rating:3A AC/DC
额定电流:3A AC/DC
- 3.Withstanding voltage:500V AC/minute
耐受电压:500V AC/分钟
- 4.Temperature range:-55℃~+105 ℃
温度范围:-55℃~+105 ℃
- 5.Insulation resistance:≥1000MΩ
绝缘电阻:≥1000MΩ
- 6.Contact resistance:≤30mΩ
接触电阻:≤30mΩ
- 7.Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0
- 8.The iron shell:SPCC-SD Nivkel Plating/Tin Plating/Gold Plating
铁壳: SPCC-SD, 镀镍/镀锡/镀金
- 9.Terminal:Copper alloy
端子: 铜合金



PART NO.:

X04 44 W I Z W 1
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Row No-Pin No: 44Pin
③Welding Board Angle:W-Male
④T:Tradutlional C:Car-pin
⑤Planting Catogtry:
1:1u 2:2u 3:3u 4:5u 5:15u 6:30u 7:AuSn
⑥Color:B-Black W-White BL-Blue
⑦1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4

铆合方式	TYPE-1: 铆合	TYPE-2: 前铆实心螺母	TYPE-3: 后铆空心螺母	TYPE-4: 后铆空心螺母锁螺丝
图示				

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: D-SUB
CHECKED		UNIT: mm/in	PART NO.: X0444WT7W1
APPROVED		SIZE: A4	DWG NO.: X-X0444WT7W1