



P.C.B LAYOUT



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:300V AC/minute

耐受电压: 300V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥500MΩ

绝缘电阻: ≥500MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

Material:PA6T UL94V-0

材质: PA6T UL94V-0

Reflow soldering temperature:260±5℃, 10S

回流焊温度: 260±5℃, 10S

X1322 W V S - 2x02 H - C40 D55 - E80
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1.Series No.

2.Category:W-Water

3.Welding Board Angle:V-Stright 180°

4.Welding Way S-SMT

5.Row No -Pin No:2xXX-2x01P-2x50P

6.Plastic height:J=1.0 mm K=1.5mm I=2.0mm

H=2.5mm D=3.0mm E=3.5mm

F=4.0mm W=5.0mm

7.Pin length: C=4.0mm

8.Pin pitch:D=5.5mm

9.Pin length:E=Plastic height+Plastic height+A

10.Planting Category:Blank=gold plating 1U"

SN=Plating Tin

AuSn=Terminal half-AuSn

V03=Plating 3U"

V15=Plating 15U"

V30=Plating 30U".....

X1322WVS-2x02H-C40D55-E80	PA6T	Brass	X1321F
PART NO	Material	Material(Pin)	Suitable XKB Female

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	1.27mm BTB Connector
CHKD	UNIT: mm/in	PART NO.:
APPD	SIZE: A4	X1322WVS-2x02H-C40D55-E80
		DWG NO.:
		X-X1322WVS-2x02H-C40D55-E80

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
	DESCRIPTION	DATE	REVISED	APPROVED		
	REVISIONS					
					UNSPECIFIED TOLERANCES	

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0