

1

2

3



4

A

B

C

D



产品字码标识

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

|                        |       |
|------------------------|-------|
| ANGULAR                | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |

| REVISIONS |         |          |                 |            |        |
|-----------|---------|----------|-----------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | 2024.05.09 | 桑 葚    |




## 规格 Specification:

- 额定值 Rating: 3A 125/250VAC
- 接触电阻 Contact resistance:  $\leq 30\text{ m}\Omega$
- 绝缘电阻 Insulation resistance:  $\geq 100\text{ M}\Omega$  (DC500V/Min)
- 电气寿命 Electronics life:  $> 10000$  cycles
- 操作力 Operation force:  $500 \pm 150\text{ gf}$
- 所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:

SS-X 03 23 S G-12 R 2 B B  
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: XKB Vertical handle;
- ② Enclosure Material:  
A-Metal case;  
BLANK-Plastic case;
- ③ Current Rating: 03-3A;
- ④ Switch Circuit: 23-2P3T;
- ⑤ S: Wire bonding;
- ⑥ Handle Shape: G-Camber handle;
- ⑦ Handle Height: 3~15mm;
- ⑧ Enclosure Shape: R-Locking rings enclosure;
- ⑨ Terminal specs:  
1:TYPE-1; 2:TYPE-2; 3:TYPE-3;  
4:TYPE-4; 5:TYPE-5;
- ⑩ Handle Colour:  
B-Black; W-White; R-Red
- ⑪ Housing Colour:  
B-Black; W-White; R-Red



XKB INDUSTRIAL PRECISION CO.,LIMITED

|                       |     |                                                                                                |                                |      |          |
|-----------------------|-----|------------------------------------------------------------------------------------------------|--------------------------------|------|----------|
| DESIGN                | 桑 葚 | VIEW:<br> | MODEL TYPE:<br>SLIDE SWITCH    |      |          |
| CHECKED               |     | UNIT: mm/in                                                                                    | PART NO.:<br>SS-0323SG-12R2BB  |      |          |
| APPROVED              |     | SIZE: A4                                                                                       | DWG NO.:<br>X-SS-0323SG-12R2BB |      |          |
| PRECISION CO.,LIMITED |     |                                                                                                | SCALE                          | PAGE | REVISION |
|                       |     |                                                                                                | N/A                            | 1/1  | A0       |

1

2

3

4

A

B

C

D