




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图片面升级整理图面	2024.07.31	阿 树



Specifications:
Voltage rating:50V AC/DC
Current rating:0.5A AC/DC
Withstanding voltage:250V AC/minute
Temperature range:-40℃~+105℃
Insulation resistance:500MΩ
Contact resistance:100mΩ




PART NO.:

X0815 F V S-80 A S-9T V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨


- 1.Series No
- 2.Category:Female
- 3.Welding Board Angle:V-Stright 180°
- 4.Welding Way:S-SMT
- 5.Row No.Pin No:XX-10-100Pin
- 6.Category:A-8.45mm Height
- 7.Special No:S-With positioning column
- 8.Material:9T-PA9T UL94V-0
- 9.Plating:Gold Plated 4u" MIN

X0815FVS-XXAS-9TV01	X0815WRS-XXAS-9TV01	/
	X0815WVS-XXBS-9TV01	11.75mm±0.5
	X0815WVS-XXCS-9TV01	24.7mm±0.5
	X0815WVS-XXDS-9TV01	9.75mm±0.5
	X0815WVS-XXES-9TV01	12.75mm±0.5
	X0815WVS-XXFS-9TV01	19.5mm±0.5
	X0815WVS-XXGS-9TV01	18.0mm±0.5
PART NO	Suitable XKB Wafer	Mating Height

Poles	Dimensions(mm)						
	A	B	C	D	E	F	G
10	6.55	4.90	3.20	12.82	7.80	10.00	13.00
20	10.55	8.90	7.20	16.82	11.80	14.00	17.00
30	14.55	12.90	11.20	20.82	15.80	18.00	21.00
40	18.55	16.90	15.20	24.82	19.80	22.00	25.00
50	22.55	20.90	19.20	28.82	23.80	26.00	29.00
60	26.55	24.90	23.20	32.82	27.80	30.00	33.00
70	30.55	28.90	27.20	36.82	31.80	34.00	37.00
80	34.55	32.90	31.20	40.82	35.80	38.00	41.00
90	38.55	36.90	35.20	44.82	39.80	42.00	45.00
100	42.55	40.90	39.20	48.82	43.80	46.00	49.00



Recommended PCB Layout
General Tolerance:±0.05



WITH CAP

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

X0815FVS-80AS-9TV01		PA9T	Phosphor Bronze	X0815W
PART NO		Material	Material(Pin)	Suitable XKB Wafer
DESIGN	阿 树	VIEW:	MODEL TYPE: 0.8mm BTB Connector	
CHECKED		UNIT: mm/in	PART NO.: X0815FVS-80AS-9TV01	
APPROVED		SIZE: A4	DWG NO.: X-X0815FVS-80AS-9TV01	
		SCALE	PAGE	REVISION
		N/A	1/1	A1