







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		pin数表更新，图片面升级整理图面	2024.08.06	阿树
A2	N/A		图框升级	2025.12.29	阿树



Specifications:
规格:
1.Voltage rating:250VAC/DC
额定电压: 250V AC/DC
2.Current rating:1A AC/DC
额定电流: 1A AC/DC
3.Withstanding voltage:500V AC/minute
耐受电压: ≥500V AC/分钟
4.Temperature range:-40℃+105℃
温度范围: -40℃+105℃
5.Insulation resistance:1000MΩMIN
绝缘电阻: ≥1000MΩ
6.Contact resistance:20mΩMax
接触电阻: ≥20mΩ
Material:
材料:
7.Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0
8.The iron shell:SPCC Nivkel Plating/Tin Plating
铁壳: SPCC,镀镍/镀锡
B、成品不能有弯针, R角不一致等不良。



PART NO.:
X08 37 W T 7 BL 1
① ② ③ ④ ⑤ ⑥ ⑦
① Series NO.
② Row No.Pin No.XX-09;15;25;37
③ Welding Board Angle :W-Male
④ T: Tradutonal C: Car-pin
⑤ Planting Categoty: 1:1U; 2:2U; 3:3U; 4:4U;
5:5U; 6:6U 7:AuSn
⑥ Color:B-BLACK;W-White;BL-Blue
⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 5:TYPE-5



NUMBER OF POSITIONS	DIMENSION				
	A±0.40	B±0.30	C±0.30	D±0.65	E±0.25
9	30.80	25.00	16.95	11.08	10.16
15	39.14	33.30	25.30	19.39	17.78
25	53.05	47.04	38.96	33.24	30.38
37	69.32	63.50	55.42	49.86	45.72

X0837WT7BL1		XDBLS		XDBLM	
PART NO		SCREW		NUT	
VIEW: 阿树		UNIT: mm/in		MODEL TYPE: D-USB	
CHECKED		SIZE: A4		PART NO.: X0837WT7BL1	
APPROVED				DWG NO.: X-X0837WT7BL1	

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN 阿树
CHECKED
APPROVED

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A2