





Specifications:

规格:

Voltage rating:125V AC/DC

额定电压: 125V AC/DC

Current rating:2A AC/DC

额定电流: 2A AC/DC

Contact Resistance:≤20MΩ

接触电阻: ≤20MΩ

Insulation Resistance:≥200MΩ

绝缘电阻:≥200MΩ

Dielectric strength:800V AC/minutenai

耐压: 800V AC/minute

X1506 H-04-PT




① ② ③ ④

① Series No

② Category:H-HSG

③ Row No:-Pin XX-02P-16P

④ Material:PT-PBT 94V-0



Poles	Dimensions(mm)			Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2	5,00	1,50	2,70	7	12,30	9,00	7,50	12	19,80	16,50	9,80
3	6,30	3,00	3,50	8	13,80	10,50	9,80	13	21,30	18,00	11,30
4	7,80	4,50	4,50	9	15,30	12,00	9,80	14	22,80	19,50	11,30
5	9,30	6,00	4,50	10	16,80	13,50	9,80	15	24,30	21,00	11,30
6	10,80	7,50	7,50	11	18,30	15,00	9,80	16	25,80	22,50	11,30

X1506H-04-PT	PBT UL 94V-0	X1506W	Tin-Plated	X1506T
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

ΔX					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
DESCRIPTION					DATE	REVISED
REVISIONS					APPROVED	

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

由 AUTODESK 学生版生成

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 1.50mm Crimp Style Connectors
DWN		VIEW:	PART NO.: X1506H-04-PT
CHKD		UNIT: mm/in	DWG NO.: X-X1506H-04-PT
APPD		SIZE: A4	WEIGHT
			SHEET
			REVISION
			1/1
			A0