



- Voltage rating: 50 V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥100MΩ
- Contact resistance: ≤20mΩ
- After environmental testing: ≤40mΩ

X1002 H-11 E-N0 HF
① ②③ ④⑤⑥

- ① Series No.
② Category : H-HSG
③ Row No.Pin No.XX-02P-20P
④ Special No:E-Have ears
⑤ Material:PT-PBT;N0-PA66 94V-0
⑥ HF-Halogen Free

Poles	Dimensione(mm)			Poles	Dimensione(mm)		
	A	B	C		A	B	C
02	1,00	5,00	2,40	13	12,00	18,00	13,40
03	2,00	6,00	3,40	14	13,00	17,00	14,40
04	3,00	7,00	4,40	15	14,00	18,00	15,40
05	4,00	8,00	5,40	16	15,00	19,00	16,40
06	5,00	9,00	6,40	17	16,00	20,00	17,40
07	6,00	10,00	7,40	18	17,00	21,00	18,40
08	7,00	11,00	8,40	19	18,00	22,00	19,40
09	8,00	12,00	9,40	20	19,00	23,00	20,40
10	9,00	13,00	10,40	22	21,00	25,00	22,40
11	10,00	14,00	11,40	24	23,00	27,00	24,40
12	11,00	15,00	12,40				

X1002H-11E-N0HF	PA66 UL 94V-0 Halogen Free	X1002T	X1002W
X1002H-11E-N0	PA66 UL 94V-0		
X1002H-11E-PT	PBT UL 94V-0		
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

							DSND		DATE		SCALE: N/A	MODEL TYPE: 1.0mm Crimp Style Connectors PART NO.: X1002H-11E-N0HF DWG NO.: X-X1002H-11E-N0HF					
						ANGLAR	±5°	DWN		DATE			VIEW: 				
ΔX						L ≤ 4	±0.2										
ΔX						4<L ≤ 16	±0.3	CHKD		DATE			UNIT: mm/in				
ΔX						16<L ≤ 63	±0.4										
MARK	DESCRIPTION				DATE	REVISED	APPROVED	L > 63	±0.5	APPD		DATE		SIZE: A4			
REVISIONS							UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn															1.0g	1/1	A0