

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	N/A		图面升级整理图面	2024.08.24	阿树

- SPECIFICATIONS
- Voltage rating:30V AC/DC
 - Current rating:0.2A AC/DC
 - Withstanding Voltage:200V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance:≥100MΩ
 - Contact resistance:≤30mΩ

PART NO.:
X0600 W R S-06-LP V01 HF
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

①Series No.
②Category: W-wafer
③Welding Board Angle: R-90°
④Row No.-Pin No.: XX-Single row
⑤Material: LP-LCP 94V-0
⑥Planting Category:V01-All Gold Flash
⑦Plug the Pin & Special NO.:HF-Halogen Free

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	0.60	3.00	12	6.60	9.00
03	1.20	3.60	13	7.20	9.60
04	1.80	4.20	14	7.80	10.20
05	2.40	4.80	15	8.40	10.80
06	3.00	5.40	16	9.00	11.40
07	3.60	6.00	17	9.60	12.00
08	4.20	6.60	18	10.20	12.60
09	4.80	7.20	19	10.80	13.20
10	5.40	7.80	20	11.40	13.80
11	6.00	8.40	22	12.60	15.00

X0600WRS-06-LPV01HF	LCP	Phosphor Bronze	X0600H
PART NO	Material	Material(Pin)	Suitable XKB Housing

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: 0.6mm Crimp Style Connector
CHECKED		UNIT:	mm/in	PART NO.: X0600WRS-06-LPV01HF
APPROVED		SIZE:	A4	DWG NO.:

SCALE	PAGE	REVISION
N/A	1/1	A1