




LEFT SIDE VIEW




BOTTOM VIEW




FRONT VIEW




RIGHT SIDE VIEW

RECOMMENDED PCB LAYOUT
VIEWED FROM COMPONENT SIDE

XKB Connectivity



TOP VIEW



BACK VIEW

XKB Connectivity

MATERIAL 材料:

HOUSING : PA66,UL94V-0,BLACK.

TERMINALS BRACKET 端子支架: PBT,UL94V-0,BLACK.

SHIELD 保护物: C2680,T=0.20MM,NICKEL PLATING ON ALL AREA.

TERMINAL 端子: PHOSPHOR BRONZE C5210,T=0.35MM,
GOLD PLATING ON CONTACT AREA.

MECHANICAL 机械:

DURABILITY 耐用性: 750 CYCLES MIN.

MATING FORCE 配合力: 23N MAX.

OPERATING TEMPERATURE 工作温度: -40°C~+85°C.

STORAGE TEMPERATURE 储存温度: -40°C~+85°C.

ALL CRITICAL DIMENSIONS WITH "±"

Electrical 电气:

1.Turn ratio 匝数比:1~2:J1~J2=1CT:1CT(±2%).

3~6:J3~J6=1CT:1CT(±2%)

2.OCL:350uH Min.at 100KHz 100mV 8mA DC.

3.Insertion Loss 插入损耗:-1.0 dB Max 1~100MHz.

4.Return loss 回波损耗:-20dB Min 1~10MHz.

-16dB Min 10~30MHz.

-12dB Min 30~60MHz.

-10dB Min 60~80MHz.

5.Cross talk: -40dB Min 1~30MHz;

-35dB Min 30~60MHz;


-30dB Min 60~100MHz;

6.CMR:-30dB Min 1~100MHz;

7.Hi-Pot:1500V AC & 2250V DC 6S 1mA PRI TO SEC.

LED Specification

Standard LED Color	LED Wavelength	Forward(A)	Forward(V)
Green	568nm	20mA	1.85-2.45V
Yellow	585nm	20mA	1.7-2.2V



广东星坤科技股份有限公司

生
熟
MARK

日期

DESCRIPTION

REVISIONS

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

文件工程章

ANGLAR
L ≤ 4
4 < L ≤ 16
16 < L ≤ 63
L > 63±5°
±0.2
±0.3
±0.4
±0.5

UNSPECIFIED TOLERANCES

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	RJ JACK
CHKD		UNIT: mm/in	PART NO.:
APPD		SIZE: A4	DWG NO.:
			X01AB002FA2DD
		WEIGHT	SHEET
		1/1	REVISIOI
			A0