

版次	工程变更单号	基本描述	日期	修订

NOTES:









1. RATED VALUE:DC 20V 3A MAX
2. DIELECTRIC WITHSTAND VOLTAGE:
100VAC.
3. TEMPERATURE RANGE:
- 25 °C ~ 85 °C.
4. CONTACT RESISTANCE:
40 MILLIONHM MAX.
5. INSULATION RESISTANCE:
100 MEGOHMS MIN.
6. INSERTION FORCE :
5N~20N.
7. UNMATING FORCE:
8N~20N.
8. DURABILITY:
10,000 CYCLES.
9. WATERPROOF RATING: IPX7.
10. ALL PRODUCTS COMPLY WITH RoHS
ENVIRONMENTAL REQUIREMENTS.
- 11: MARK "▼" AS THE FOCUS,
FIRST ITEM INSPECTION.
- 12: MARK "⊗" TO MEASURE DIMENSIONS
FOR FAI.

TABLE:

环氧树脂			
外壳		SUS304R-1/2H.T=0.20mm	Ni:50u"Min;
内壳		SUS304R-1/2H.T=0.30mm	Ni:50u"Min;
护套		PA9T(G.F30%).BLACK.	/
品名 MD半成品	端子	C2680R-H.T=0.15mm	Ni:30u"Min; Au:CONTACT AREA:1u" Solder AREA:G/F
	塑胶	LCP(G.F30%) BLACK.	/
PART NAME		MATERIALS	FINISH


 **韩下** 深圳市韩下电子有限公司

品名规格	HX-TYPE-C 16P IPX7-B-L8.15				设计	李春风
未注公差:	料号				审核	钟华华
.000 ±0.10 .00 ±0.20 .0 ±0.30 角度 ±1°	图纸类型	成品图	比例	1:1	核准	罗小春
视角		版本	A/0	单位	MM	



RECOMMEND P.C.B LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

防水圖:



- 1: 材料: 黑色硅胶, 符合ROHS环境管理物质.
2: 尺寸: 外径:10.64*4.86*1.50mm.

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SUB1	VBUS			GND
GND			VBUS	SUB2	D-	D+	CC1	VBUS			GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1



深圳市韩下电子有限公司
Shenzhen Hanxia Electronic Co., Ltd
Tel: 0755-23086569

承 认 书

SPECIFICATION FOR APPROVAL

产 品 编 码
Material code:

产品名称 Project:

TYPE-C

规格型号 Part No:

HX-TYPE-C 16P IPX7-B-L8.15

贵公司承认印 Approval signatures

料 号/Part No.	签 章/Signatures

日期 Date:

拟制/Drawn	黄彬	
审核/Check	张伟	
批准/Approved	罗小春	