








REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.09.05	
/	N/A		/	/	/



- Specification
- | | |
|-------------------------|------------------|
| 1.Voltage rating | 250V AC/DC. |
| 2.Current Rating | 3A AC/DC. |
| 3.Withstanding Voltage | 1500V AC/Minute. |
| 4.Temperature Rangel | -40 ~+125 . |
| 5. Contact Resistance | 20 mΩ Max. |
| 6.Insulation Resistance | 1000 MΩ Min. |

PART NO.:
X9555 I-P SN-A2

Series Number.
Category: T-terminal
Material: P-Phosphorous bronze
Finish:SN-Tin-plated
Other Types A2-Tight Type



X9555T-PSN-A2	Phosphor Bronze	AWG#22-28	Tin Pated	X9555H-B(2x02~2x13 X9555H-B1(2x02~2x13 X9555H-B2(2x02~2x13 X9555H-B3(2x02~2x13 X9555H-A1(2x02~2x13 X9555H-A2(2x02~2x13 X9555H-A3(2x02~2x13
PART NO	Material	Wire Range	Finish	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: 2.54mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X9555T-PSN-A2
APPROVED		SIZE: A4	DWG NO.: