

1

2

3

4

A

B

C


D

A

B

C




D



| REVISIONS |         |          |                 |           |        |
|-----------|---------|----------|-----------------|-----------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE      | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | /         | /      |
| A1        | N/A     |          | 图面升级整理图面        | 2024.9.06 | 阿树     |

#### ■SPECIFICATIONS

- Voltage rating:250V AC/DC
- Current rating:3A AC/DC
- Withstanding Voltage:1000V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥500MΩ
- Contact resistance:≤20mΩ



PART NO.:

X1511 H-11 L-N0  
① ② ③ ④ ⑤

- ①Series No  
②Category:H-HSG  
③Row No.Pin No:XX-02~15P  
④Special N0:L-With Lock  
⑤Material:N0-Nylon 66 UL94V-0

| Poles | Dimensions(mm) |       |       |
|-------|----------------|-------|-------|
|       | A              | B     | C     |
| 02    | 1.50           | 4.10  | 3.30  |
| 03    | 3.00           | 5.60  | 4.80  |
| 04    | 4.50           | 7.10  | 6.30  |
| 05    | 6.00           | 8.60  | 7.80  |
| 06    | 7.50           | 10.10 | 9.30  |
| 07    | 9.00           | 11.60 | 10.80 |
| 08    | 10.50          | 13.10 | 12.30 |
| 09    | 12.00          | 14.60 | 13.80 |
| 10    | 13.50          | 16.10 | 15.30 |
| 11    | 15.00          | 17.60 | 16.80 |
| 12    | 16.50          | 19.10 | 18.30 |
| 13    | 18.00          | 20.60 | 19.80 |
| 14    | 19.50          | 22.10 | 21.30 |
| 15    | 21.00          | 23.60 | 22.80 |

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



|          |    |             |                                              |
|----------|----|-------------|----------------------------------------------|
| DESIGN   | 阿树 | VIEW:       | MODEL TYPE:<br>1.50mm Crimp Style Connectors |
| CHECKED  |    | UNIT: mm/in | PART NO.:<br>X1511H-11L-N0                   |
| APPROVED |    | SIZE: A4    | DWG NO.:<br>X-X1511H-11L-N0                  |
|          |    | SCALE       | PAGE                                         |
|          |    | N/A         | 1/1                                          |
|          |    | REVISION    | A1                                           |