


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2025.12.19	
A2	ECN-P-2026032601			2026.03.26	



- SPECIFICATIONS
- Voltage rating: 125V AC/DC
 - Current rating: 1A AC/DC
 - Withstanding Voltage: 250V AC/minute
 - Temperature range: -40°C ~ +125°C
 - Insulation resistance: $\geq 100M\Omega$
 - Contact resistance: $\leq 20m\Omega$

PART NO.:

X9821 I F-P SN

Series Number.
Category: T-terminal
Category: F-Female Terminal
Material: P-Phosphor Bronze
Plating Category: SN-Bright Tin Plating

X9821TF-PSN	Phosphor Bronze	AWG#28-32	1.0mm(Max)	Tin Plated	X9821HM-PSN
PART NO	Material	Wire Range	Insulation O.D.	Finish	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	VIEW:	MODEL TYPE: 1.25mm Crimp Style Connectors
CHECKED	UNIT: mm/in	PART NO.: X9821TF-PSN
APPROVED	SIZE: A4	DWG NO.: