






- X9556 W R -19-N0V01
- 11 12 13 14 15 16 17 18 19
- 11 Series No.
12 Category :
W-wafer
13 Welding Board Angle:
R-90°
14 Welding Way:
Blank-DIP
15 Row No.-Pin No.
XX-Single row
16 Special NO.
17 Material :
N0-PA66 94V-0
18 Planting Category:
V**All Gold-Plated
"01-1u" ; "02-2u" ; "03-3u" ; "05-5u"
"10-10u" ; "15-15 u" ; "30-30u" ; "50-50u"
SN-Bright tin plating 70U"
SN1-Bright tin plating 120U"Min. ;
SW-Fog Tin plating
19 Color:
Blank-natural color

Poles	Dimensions (mm)	
	A	B
2	2.54	7.62
3	5.08	10.16
4	7.62	12.70
5	10.16	15.24
6	12.70	17.78
7	15.24	20.32
8	17.78	22.86
9	20.32	25.40
10	22.86	27.94
11	25.40	30.48
12	27.94	33.02
13	30.48	35.56
14	33.02	38.10
15	35.56	40.64
16	38.10	43.18
17	40.64	45.72
18	43.18	48.26
19	45.72	50.80
20	48.26	53.34
21	50.80	55.88
22	53.34	58.42
23	55.88	60.96
24	58.42	63.50

X9556WR-19-N0V01	Nylon 66 UL 94V-0	Brass	Gold-Flash	X9556H
PART N0	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

XKB						DSND		DATE		SCALE: N/A	MODEL TYPE:			
				XKB	ANGLAR	±5°	DWN		DATE	VIEW: 	2.54 mm Crimp Style Connectors			
Δx					L≤4	±0.2	CHKD		DATE	UNIT: mm/in	PART NO.: X9556WR-19-N0V01			
Δx					4<L≤16	±0.3			DATE			DWG NO.: X-X9556WR-19-N0V01		
Δx					16<L≤63	±0.4			DATE					
MARK	DESCRIPTION			DATE	REVISED	APPROVED	APPD		DATE		SIZE: A4			
REVISIONS						UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET	REVISION
www.helloxkb.com												1.0g	1/1	A0