

rs





1

2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.04.01	阿树
/	N/A		/	/	/


**■SPECIFICATIONS**

- Voltage rating:600V AC/DC
- Current rating:9A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:-45°C+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤20mΩ

PART NO.:

X9357 H M-2X11 N2
① ② ③ ④ ⑤

- ①Series No
②Category:H-HSG
③Welding Board Angle:M-Male HGS
④Row No.-Pin No.:2X11P
⑤Material:N2-PA66 94V-2 White



X9357HM-2x11-N2	PA66	X9357W-A	X9357HF
PART NO	Material	Suitable XBK Wafer	Suitable XBK Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 4.20 mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X9357HM-2x11-N2
APPROVED		SIZE: A4	DWG NO.: X-X9357HM-2x11-N2
SCALE	N/A	PAGE	REVISION
		1/1	A0

1

2

3

4