








01:AU 1U"Min			
03:AU 3U"Min	1:PBT		W:WHITE
05:AU 5U"Min	2:PA6T		B:BLACK
10:AU 10U"Min	3:PA9T		
15:AU 15U"Min	4:LCP		
30: AU 30U"Min			

L	
1	8.17
2	9.17

							DSND		SCALE: N/A	MODEL TYPE: Type-C 3.1		
ΔX					ANGLAR	$\pm 5^\circ$		DWN		VIEW: 	PART NO.: U262-243N-3BVC80-2	
ΔX					$L \leq 4$	± 0.2		CHKD		UNIT: mm/in	DWG NO.: X-U262-243N-3BVC80-2	
ΔX					$4 < L \leq 16$	± 0.3		APPD		SIZE: A4		
ΔX					$16 < L \leq 63$	± 0.4						
MARK	DESCRIPTION	DATE	REVISED	APPROVED	$L > 63$	± 0.5						
							UNSPECIFIED TOLERANCES			KKB INDUSTRIAL PRECISION CO.,LIMITED		
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn										WEIGHT	SHEET 1/1	REVISION A0