

1





2

3


4

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.26	阿树



Specifications:
Voltage rating:30V AC/DC
Current rating:0.5A AC/DC
Withstanding voltage:500V AC/minute
Temperature range:-40~+55℃
Insulation resistance:≥100MΩ
Contact resistance:≤30mΩ
After environmental testing:≤20mΩ
Operating Life(Cycles):5000
Mating Force:3-20N



Plastic	PA	
Terminal 3	Phosphor Bronze	Ag
Terminal 2	Phosphor Bronze	Ag
Terminal 1	Phosphor Bronze	Ag
PAPT NAMF	MATERIAL	PLATING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN
CHECKED
APPROVED

阿树

VIEW:

UNIT: mm/in

SIZE: A4

MODEL TYPE:
3.5 PHONE JACKPART NO.:
PJ-313D-B-SMTDWG NO.:
X-PJ-313D-B-SMT

SCALE	PAGE	REVISION
N/A	1/1	A1

1

2

3

4

www.helloxkb.com

www.helloxkb.cn

www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED