





RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.05.18

Technical Data
Material:
Contact Material:Copper Alloy
Contact Plating: Au or Sn Over Ni
Insulator Material:PBT/PPS UL94V-0

Electrical:
Rating current:3Amps/contact max
Rating voltage:60V AC/DC
Contact resistance:≤4MΩ/contact
Insulation resistance:≥1000MΩ
withstanding Voltage:500V AC/minute

Mechanical:
Operaing temperatures:-40℃ to +105℃
Soldering temperature:+255℃ MAX(PPS)



P.C.B LAYOUT

X.±0.50	X.°±	PART NO: IC254V-12-12-1000A		XFCN 兴飞连接器		
.X±0.25	.X°±					
.XX±0.15	.XX°±	TITLE: 2.54mm IC Socket Connectors		0769-82001899		
.XXX±0.10	.XXX°±			www.xfconn.com		
UNITS:	mm			DWG NO: /		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD	Chen ZhiQiang			
		CHKD	Liu Wei	VIEW		
		DRAW	Chen HongJiang	SCALE	SHEET	REV
		DATE	2024.05.18	NONE	1/1	A1