


1. View and size(视图及尺寸)

Main technical indicators(主要技术指标)	
1.Mating (插拔次数)	5000
2.Working Temperature (温度)	-55~+150℃
3.IP Rating (防护级别)	IP 50
4.Diameter of socket end(插合端直径)	φ0.7
5.Testing Voltage (测试电压)	1150V
6.Working Voltage (工作电压)	1350V
7.Rated Current (额定电流)	6.5A
8.Shell material(壳体材质)	Brass (chromium plating)/nickel plating) fixation ring/ 黄铜(镀铬)/镍(镀镍) 固定圈
9.Pin Material(插针材料)	Copper alloy gold plating(铜合金镀金)
10.Insulator material(绝缘体材质)	PPS

Sum up(总结)	
Series(系列)	B
Shell style/model (外壳样式/型号)	ZGG-With a nut (post-fixed)带有一个螺母(后固定)
Button (按键)	A button(一个按键)
Termination type (终止类型)	Mother solder tin(母焊锡)
Line diameter awg(线材直径)	30AWG-22AWG
Cable diameterφ (电缆直径)	φ1.4-9.9MM
Match plug(匹配插头)	TGG.2B.P14.CLAD52H

Location pin combination(定位销组合)				
(编号) Numder	Number of positioning pins(定位销数量)	Angle(角度)	Series(系列)-2B	
G	One(1)		(Zero degrees)0°	
A	Two(2)	A	Thirty degrees(30°)	
B	Two(2)		Forty-five degrees(45°)	
C	Two(2)		Sixty degrees(60°)	
D	Two(2)	Y	95 degrees (95°)	
E	Two(2)	β	120 degrees(120°)	
F	Two(2)		145 degrees(145°)	
J	Two(2)	A	37.5degrees(37.5°)	
K	Two(2)		52.5degrees(52.5°)	
L	Two(2)	Y	Seventy degrees(70°)	


	A	B	C-V	ANGLE	
5-10	±0.02	±0.05	±0.1	0°-30°	±0.1°
50-100	±0.1	±0.15	±0.2	61°-90°	±0.5°
50-100	±0.15	±0.2	±0.25		
100-	±0.15%	±0.20%	±0.25%		



	A	L	E	S1	S2
MM	φ18	18.5	M15*1	13.5	17
in	0.71	0.73		0.53	0.67




Welded surface
(焊接面)



Pane hole size
(面板开孔尺寸)



(Welded mother
adhesive core)
焊接型母胶芯



Positive view of the socket
(插座正视图)

ZG G.2B.P14.C.L.L

Model(型号)

Positioning pin(定位销)

Series(系列)

Needle core configuration(针芯配置)

Outer casing(外壳)

Insulator(绝缘体)

Needle core(针芯)

DESIGNED(设计)		DATE(日期)		SCALE(比例)	N/A(不适用)	MODEL TYPE 型号类型: ZGG.2B.P14.C.L.L
CHECKED(校对)		DATE(日期)		VIEW(视图)		PART NO. 2B14 core socket
APPROVED(审核)		DATE(日期)		UNIT(单位)	MM	名称: 2B14芯插座
REVISIONS				MATERIAL(材料)		DWG NO.:
www.helloxb.com www.helloxb.cn				XKB INDUSTRIAL PRECISION CO.,LIMITED		WEIGHT(重量)
						SHEET(张)
						1/1
						REVISION(修订)
						A0