


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.22	阿树



Specifications:

规格:

1.Voltage rating:250VAC/DC
额定电压: 250V AC/DC

2.Current rating:3A AC/DC
额定电流: 3A AC/DC

3.Withstanding voltage:500V AC/minute
耐受电压: 500V AC/分钟

4.Temperature range: -55℃-+105℃
温度范围: -55℃-+105℃

5.Insulation resistance:1000MΩ MIN
绝缘电阻: 1000MΩ MIN

6.Contact resistance:30mΩ Max
接触电阻: 30mΩ Max

Material:

材料:

7.Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0



8.The iron shell:SPCC-SD Nivkel Plating/Tin Plating/Gold Plating
铁壳: SPCC-SD,镀镍/镀锡/镀金

9.Terminal:Copper alloy
端子: 铜合金

PART NO.:

X01 09 F I Z B 3
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series NO.
- ②Row No.Pin No.XX-09;15;25;37
- ③Welding Board Angle :F-Female
- ④T: Tradutonal C: Car-pin
- ⑤Planting Categyry: 1:1U' 2:2U' 3:3U' 4:5U' 5:15U'
- ⑥Color:B-BLACK W-White BL-Blue
- ⑦1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4



NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
9	16.35	24.99	30.80	19.28
15	24.75	33.30	39.20	27.65
25	38.35	47.04	53.05	41.28
37	54.75	63.50	69.40	57.71

铜合方式	TYPE-1: 铜合	TYPE-2: 前铜实心螺母	TYPE-3: 后铜空心螺母	TYPE-4: 后铜空心螺母锁螺丝
图示				

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuces	



DESIGN	阿树	VIEW:	MODEL TYPE: D-SUB
CHECKED		UNIT: mm/in	PART NO.: X0109FT7B3
APPROVED		SIZE: A4	DWG NO.: X0109FT7B3